

SIGNAL MINI DISPLAYPORT

V4

DIRECT DEVICE INTEGRATION ON PCB				
	HARTING PushPull Mini DisplayPort bulkhead housing, plastic, for device integration	Compact housing	09 45 545 0042	
		Mini DisplayPort jack, angled	09 45 551 1000	
		Adapter for the integration of the Mini DisplayPort jack into the Compact housing	09 45 545 1002	
SYSTEM CABLE				
	HARTING PushPull Mini DisplayPort system cable, 20 poles, black, TPE, AWG 32, both sides assembled	DisplayPort 1.2, both sides PushPull	0.5 m	09 45 145 1000
		DisplayPort 1.2, both sides PushPull	1.0 m	09 45 145 1001
		DisplayPort 1.2, both sides PushPull	1.5 m	09 45 145 1002
		DisplayPort 1.2, both sides PushPull	2.0 m	09 45 145 1003
		DisplayPort 1.1, both sides PushPull	3.0 m	09 45 145 1004
		DisplayPort 1.2 PushPull / IP20	0.5 m	09 45 145 1010
		DisplayPort 1.2 PushPull / IP20	1.0 m	09 45 145 1011
		DisplayPort 1.2 PushPull / IP20	1.5 m	09 45 145 1012
		DisplayPort 1.2 PushPull / IP20	2.0 m	09 45 145 1013
DisplayPort 1.1 PushPull / IP20	3.0 m	09 45 145 1014		

SIGNAL 10 POLES / 20 POLES

V4

DEVICE INTEGRATION ON PCB			
	HARTING PushPull Signal jack insert, 10 poles, 50 V / 5 A	Compact housing, without fixing clip, angled	09 45 545 0043
		Compact housing, with fixing clip	09 45 545 0042
		Compact housing, without fixing clip, straight	09 45 545 0040
		Signal solder jack, straight	09 45 545 9012
		Signal solder jack, angled	09 45 545 9011
DEVICE INTEGRATION WITH PANEL FEED-THROUGH			
	HARTING PushPull Signal panel feed-through, 50 V / 5 A, plastic	Compact housing, 10 poles, without insert	09 45 545 0041
		System cable (1 m) with compact housing, 10 poles System cable (1 m) with compact housing, 20 poles Insert for crimp contacts (Order male D-Sub contacts separately)	09 48 430 08A6 010 33 22 143 0500 002 09 45 545 9010
CONNECTOR CABLE SIDE			
	HARTING PushPull Signal connector, 10 poles, 50 V / 5 A, plastic	Connector for crimp contacts (Order female D-Sub contacts separately)	09 45 145 9011
		SYSTEM CABLE	
	HARTING PushPull system cable, 10 poles, AWG 20, PVC (other cable types and lengths on request)	0.5 m	09 48 313 18A6 005
		1.0 m	09 48 313 18A6 010
		2.0 m	09 48 313 18A6 020
		5.0 m	09 48 313 18A6 050
	HARTING PushPull system cable, 20 poles, 0.14 mm <sup>2</sup> , PUR (other cable types and lengths on request)	0.5 m	09 48 353 5848 005
		1.0 m	09 48 353 5848 010
		2.0 m	09 48 353 5848 020
		5.0 m	09 48 353 5848 050

V14

DEVICE INTEGRATION ON PCB			
	Han® PushPull Signal jack insert, 10 poles, 50 V / 5 A	Metal housing, rectangular	09 35 002 0303
		Plastic housing, rectangular	09 35 002 0323
		Signal solder jack, straight	09 35 002 6002
		Signal solder jack, angled	09 35 002 6001
DEVICE INTEGRATION WITH PANEL FEED-THROUGH			
	Han® PushPull Signal panel feed-through, 10 poles, 50 V / 5 A	Metal housing, rectangular	09 35 012 0311
		Metal housing, circular Plastic housing, rectangular Insert for crimp contacts (Order male D-Sub contacts separately)	09 35 012 0312 09 35 012 0331 09 45 545 9010
CONNECTOR CABLE SIDE			
	Han® PushPull Signal connector, 10 poles, 50 V / 5 A	Metal connector for crimp contacts	6.5 - 9.5 mm
		Plastic connector for crimp contacts	9 - 13 mm
		Plastic connector for crimp contacts	4 - 6.5 mm
		Plastic connector for crimp contacts (Order female D-Sub contacts separately)	09 35 261 0401 09 35 261 0421 09 35 261 0423 09 35 262 0423
ACCESSORIES			
	Han® PushPull Signal cable coupling, 10 poles, 50 V / 5 A	Cable coupling, metal	61 04 201 1086