






Number of contacts

2

16 A 2.900/5.000 V 15 kV 3

Modular

| Identification | Conductor cross-section (mm ²) | Part number | | Drawing (dimensions in mm) |
|--|--|--|--|---|
| | | Male | Female | |
| <p>Han-Modular®, Han® HV module, for Han E® crimp contacts, Crimp termination,</p> <p>Pack contents: 1 module, 2 locking sleeves, 2 heat shrink tubes</p>  <p>Please order crimp contacts separately.</p> | 0.5 ... 4 | 09 14 002 3021 | 09 14 002 3121 | <p>Assembly instructions</p>  <p>ATTENTION! Stripping length 9.5 mm Crimp with crimping tool 09 99 000 0888 Snap crimped cable in the insert. Shrink the heat shrink tube over the rear of contact.</p>   |
| <p>Han E®, Crimp contact, Contact surface: Silver plated</p>  | 0.5 0.75 1 1.5 2.5 3 4 | 09 33 000 6121 09 33 000 6114 09 33 000 6105 09 33 000 6104 09 33 000 6102 09 33 000 6106 09 33 000 6107 | 09 33 000 6220 09 33 000 6214 09 33 000 6205 09 33 000 6204 09 33 000 6202 09 33 000 6206 09 33 000 6207 | |