

Identification	Conductor cross-section (mm ²)	Part number	
Han-Port®, Socket, 2 cut-outs for HIFF data module, Finger safe, Screw termination, Great Britain (BS), 30 mm / 250 V AC / 60 Hz, 50 Hz / 13 A	4	39 50 001 0452	
Han-Port®, Socket, 2 cut-outs for HIFF data module, Screw termination, China, 43 mm / 250 V AC / 50 Hz / 10 A	4	39 50 001 0458	
Han-Port®, Socket, Screw termination, China, 43 mm / 250 V AC / 50 Hz / 10 A 1x RJ45 Cat.6 / 1x USB-A 3.0, enclosed separately	4	39 50 012 0458	
Han-Port®, Socket, 2 cut-outs for HIFF data module, Spring clamp termination, Germany (VDE), 43 mm / 250 V AC / 50 Hz / 16 A	2.5	39 50 001 0450	
Han-Port®, Socket, 2 cut-outs for HIFF data module, Spring clamp termination, Switzerland, 30 mm / 250 V AC / 50 Hz / 10 A	1.5	39 50 001 0454	
Han-Port®, Socket, Spring clamp termination, Germany (VDE), 43 mm / 250 V AC / 50 Hz / 16 A 1x RJ45 Cat.6 / 1x USB-A 3.0, enclosed separately	2.5	39 50 012 0450	