



Number of contacts

**4+**

40 A 400/690 V 6 kV 3  
 10 A 250 V 4 kV 3  
 + 2 additional signal contacts



Han Q

Identification	Conductor cross-section (mm <sup>2</sup> )	Part number		Drawing (dimensions in mm)
		Male	Female	
Han® Q, 4/2, Axial screw termination, Contact surface: Silver plated  With Han-Quick Lock® signal contacts	2.5 ... 6, 0.25 ... 1.5 Signal 4 ... 10, 0.25 ... 1.5 Signal	09 12 006 2662 09 12 006 2663	09 12 006 2762 09 12 006 2763	 Stripping length Power contacts 8 mm Stripping length Signal contacts 10 mm Tightening torque 1.8 Nm
Han® Q, 4/2, Axial screw termination, Contact surface: Silver plated Without signal contacts	2.5 ... 6 4 ... 10	09 12 006 2665 09 12 006 2666	09 12 006 2765 09 12 006 2766	