Han-Drive® hoods/housings



Features

- Angled housing replaces the terminal box
- Compact design saves space
- The position of the terminal housing can be switched by 90°
- Compatible with standard hoods for single lever size 10 B
- Locking levers: Han-Easy Lock®
- Star and delta circuits can be realised in the female connector Han® ESS
- Suitable for standard inserts

Technical characteristics

-40 ... +125 °C Limiting temperature

Degree of protection acc. to IEC IP65 60529

Type rating acc. to UL 50 / UL 50E 4, 4X, 12

Material (hood/housing) Aluminium die-cast Surface (hood/housing) Uncoated, Powder-coated Colour (hood/housing) RAL 7037 (dust grey)

Material (seal)

Material (locking) Polycarbonate (PC), Stainless

steel

Colour (locking) RAL 7037 (dust grey) V-0

Material flammability class acc.

to UL 94 (locking levers)

compliant

Specifications and approvals

DNV GL

 $C \in$