







Number of contacts

6

16 A 500 V 6 kV 3

Modular

Identification	Conductor cross-section (mm ²)	Part number		Drawing (dimensions in mm)																		
		Male	Female																			
Han-Modular [®] , Han E [®] module, Han-Quick Lock [®] termination, Contact surface: Silver plated 	0.5 ... 2.5	09 14 006 2633	09 14 006 2733																			
Han-Modular [®] , Han E [®] module, Crimp termination Please order crimp contacts separately. 	0.14 ... 4	09 14 006 3001	09 14 006 3101	 <p>Contact arrangement (view from termination side)</p>																		
Han E [®] , Crimp contact, Contact surface: Silver plated 	0.14 ... 0.37 0.5 0.75 1 1.5 2.5 3 4	09 33 000 6127 09 33 000 6121 09 33 000 6114 09 33 000 6105 09 33 000 6104 09 33 000 6102 09 33 000 6106 09 33 000 6107	09 33 000 6227 09 33 000 6220 09 33 000 6214 09 33 000 6205 09 33 000 6204 09 33 000 6202 09 33 000 6206 09 33 000 6207	 <table border="1"> <thead> <tr> <th>Conductor cross-section</th> <th>Identification</th> </tr> </thead> <tbody> <tr> <td>0.14-0.37 mm² AWG 26-22</td> <td>no groove</td> </tr> <tr> <td>0.5 mm² AWG 20</td> <td>no groove</td> </tr> <tr> <td>0.75 mm² AWG 18</td> <td>1 groove*</td> </tr> <tr> <td>1 mm² AWG 18</td> <td>1 groove</td> </tr> <tr> <td>1.5 mm² AWG 16</td> <td>2 groove</td> </tr> <tr> <td>2.5 mm² AWG 14</td> <td>3 groove</td> </tr> <tr> <td>3 mm² AWG 12</td> <td>wide groove</td> </tr> <tr> <td>4 mm² AWG 12</td> <td>no groove</td> </tr> </tbody> </table> <p>* on the back crimp collar</p>	Conductor cross-section	Identification	0.14-0.37 mm ² AWG 26-22	no groove	0.5 mm ² AWG 20	no groove	0.75 mm ² AWG 18	1 groove*	1 mm ² AWG 18	1 groove	1.5 mm ² AWG 16	2 groove	2.5 mm ² AWG 14	3 groove	3 mm ² AWG 12	wide groove	4 mm ² AWG 12	no groove
Conductor cross-section	Identification																					
0.14-0.37 mm ² AWG 26-22	no groove																					
0.5 mm ² AWG 20	no groove																					
0.75 mm ² AWG 18	1 groove*																					
1 mm ² AWG 18	1 groove																					
1.5 mm ² AWG 16	2 groove																					
2.5 mm ² AWG 14	3 groove																					
3 mm ² AWG 12	wide groove																					
4 mm ² AWG 12	no groove																					