

Number of contacts

# 6+

16 A 500 V 6 kV 3

Han  
HMC

Identification	Conductor cross-section (mm <sup>2</sup> )	Part number		Drawing (dimensions in mm)
		Male	Female	
<p>Han® ES Press HMC, Cage-clamp termination, Contact surface: HMC gold plated</p> <p>for hoods/housings high construction only Blue slide</p>	0.14 ... 2.5	09 33 206 2648	09 33 206 2748	<p>Distance for contact max. 21 mm</p> <p>Contact arrangement (view from termination side)</p> <p>Panel cut out</p>