





Number of contacts

64+

16 A 500 V 6 kV 3

Han
HMC

Identification	Conductor cross-section (mm ²)	Part number		Drawing (dimensions in mm)
		Male	Female	
<p>Han® EEE HMC, Crimp termination</p>  <p>Please order crimp contacts separately.</p>	0.14 ... 4	09 32 264 3001	09 32 264 3101	 <p>1) distance for contact max. 21 mm</p>  <p>Contact arrangement (view from termination side)</p>  <p>Panel cut out</p>