

Features

- Modular assembly
- Robust design
- Suitable for standard and EMC hoods and housings
- Low wiring costs

Technical characteristics

Rated current	40 A
Rated voltage	500 V
Rated impulse voltage	6 kV
Pollution degree	3
Contact resistance	≤3 mΩ
Limiting temperature	-40 ... +125 °C
Material (insert)	Polycarbonate (PC)
Material (contacts)	Copper alloy
RoHS	compliant with exemption

Specifications and approvals

EN 60664-1
IEC 61984

Details

Hinged frames see chapter Han 06

Identification	Part number		Drawing (dimensions in mm)
	Male	Female	
Han [®] C, PCB contact, Contact surface: Silver plated	09 32 000 6295		
PCB adapter, In the Han [®] 40 A Axial module	09 14 002 2603	09 14 002 2703	