


M12 Panel feed-through A-coded







Mating face



A-coding
Mating face
acc. to IEC 61076-2-101



Circular
Connectors

Identification	Part number	Drawing	Dimensions in mm
<p>M12 Panel feed-through</p>  <p>Female A-coding, 50 cm conductors, 0.5 mm², 4 poles</p> <p>Panel thickness min. 2.0 mm max. 5.0 mm</p>	<p>21 03 311 2400</p>		
<p>M12 Panel feed-through</p>  <p>Female A-coding, 50 cm conductors, 0.5 mm², 5 poles</p> <p>Panel thickness min. 2.0 mm max. 5.0 mm</p>	<p>21 03 311 2501</p>	