



Han® 3 A 2 x LC duplex

Advantages

- Compact, space-saving Design
- Just one LWL modul for high mechanical load
- High packing density
- A & B parts identification according to TIA 568 standard

Technical characteristics

Degree of protection	IP65 / IP67
Temperature range	-40 °C ... +70 °C
Housing material	Zinc die-cast powder coating black

Identification	Part number	Drawing	Dimensions in mm
Components device side Multimode GOF Singlemode GOF	09 57 467 0004 000 09 57 467 0005 000		
Connector Multimode GOF Singlemode GOF	09 57 407 0001 000 09 57 407 0002 000		