

Crimp contacts for high density connectors



Identification	Wire gauge (mm ²)	Part number			
		stamped male contacts		stamped female contacts	
		Performance level 3	S4 ¹⁾	Performance level 3	S4 ¹⁾
Performance levels Explanations see page 05.04 Other performance levels on request					
500 pieces/box	AWG 26-24 0.14-0.22 stranded	09 56 000 8177	09 56 000 8175	09 56 000 8277	09 56 000 8275
500 pieces/reel Unrolling left		09 56 000 8167	09 56 000 8165	09 56 000 8267	09 56 000 8265
10 000 pieces/reel Unrolling left		09 56 000 8157	09 56 000 8155	09 56 000 8257	09 56 000 8255
Unrolling direction		<p>500 pieces/reel Unrolling left 10 000 pieces/reel Unrolling left</p> <p>for HARTING tools</p>			

D-Sub

¹⁾ S4 = 0.76 µm (30 µinch) Au or PdNi equivalent
Contact dimensions see page 05.41