



Ethernet Switch

Ha-VIS FTS 3100-A-PTP

10-port Ethernet Switch with Fast Track Switching Technology, managed

Managed	IP30	PROFINET compatible <input checked="" type="checkbox"/>	EtherNet/IP compatible <input checked="" type="checkbox"/>
Number of ports, Copper / Termination	10x 10/100Base-TX / RJ45 (Twisted Pair)		
Input voltage / Termination	24 V $\overline{=}$ / 5-pole, pluggable screw contact, for redundant power supply		
Permissible range (min./max.)	9.6 V ... 60 V $\overline{=}$		
Input current	approx. 300 mA (at 24 V DC)		
Housing material	aluminium, anodised		
Dimensions (W x H x D)	44 x 130 x 100 mm (without connectors)		
weight	approx. 0.5 kg		
Working temperature	0 °C ... +70 °C		
Approvals	UL 508; UL 60 950-1; DNV		
Time synchronization	Precision Time Protocol (PTP) hardware based		

Ha-VIS FTS

Identification	Part number	Drawing	Dimensions in mm
----------------	-------------	---------	------------------

Ha-VIS FTS 3100-A-PTP
Ethernet Switch with
10 RJ45 ports

20 78 110 4001

