


Number of contacts

64



Female connectors

DIN Signal
up to 2 A

Identification	No. of contacts	Contact arrangement	Part number 3	Performance levels according to IEC 60603-2. Explanation chapter 00	
				2	1
Female connector with solder pins 2.9 mm	64		Performance level 3 on request	09 02 264 6824 09 02 464 6824 ^{b)} 09 02 764 6824 ^{c)}	09 02 264 2824
	64			09 02 264 6841 ^{d)}	
Female connector with solder pins 4.5 mm	64			09 02 264 6825 09 02 264 6825 222 ^{f)} 09 02 464 6825 ^{b)} 09 02 764 6825 ^{c)}	09 02 264 2825
	64			09 02 264 6829 ^{d)}	
Female connector with solder pins 13 mm	64			09 02 264 6421	
Female connector with press-in pins 4.5 mm	64			09 02 264 6850 09 02 264 6850 222 ^{f)}	09 02 264 2850
Female connector with press-in pins 13 mm	64			09 02 264 6861 ^{a)}	
Female connector with wrap posts ¹⁾ 13 mm	64			09 02 264 6821	
Female connector with solder lugs 5.5 mm	64		09 02 264 6823		

01
12

¹⁾ To be used only for wire wrap termination

^{a)} Contacts for rear interfacing selectively gold plated (performance level 3)

^{b)} Connectors with snap-in clips see chapter 00

^{c)} Connectors with coding see chapter 00

^{d)} CTI > 400

^{f)} Railway classification NFF 16-101, Smoke index: F1, Flammability class: I2
Other contact arrangements on request