


Number of contacts

96, 64, 32



Female connectors

Identification	No. of contacts	Contact arrangement	Part number Performance levels according to IEC 60603-2. Explanation chapter 00			
			3	2	1	
Female connector Type C with press-in terminations 4.5 mm with press-in terminations for rear interfacing Usage of HARTING shroud recommended: contacts for rear interfacing selectively gold plated (performance level 3) 13 mm 16.2 mm 17 mm with press-in terminations for wire wrapping (wrap posts not for interfacing, no performance level) 13 mm 17 mm	96		09 03 296 7850	09 03 296 6850 09 03 296 6850 222 ^{f)} 09 03 796 6850 ^{c)} 09 03 796 6850 222 ^{c)f)}	09 03 296 2850 09 03 296 2850 222 ^{f)}	
	64		09 03 264 7850	09 03 264 6850 09 03 264 6850 222 ^{f)} 09 03 764 6850 ^{c)}	09 03 264 2850	
	32			09 03 232 6850	09 03 232 2850	
	96				09 03 296 6861 09 03 796 6861 ^{c)}	
	64				09 03 264 6861	
	96				09 03 296 6411 09 03 296 6416 ²⁾	
	64				09 03 264 6411	
	32				09 03 232 6411	
	96				09 03 296 6862 09 03 796 6862 ^{c)}	
	64				09 03 264 6862	
	96				09 03 296 6851 252	
	64				09 03 264 6851 252	
96					09 03 296 2852 252	

²⁾ Contacts for rear interfacing gold plated (performance level 2)

^{c)} Connectors with coding see chapter 00

^{f)} Railway classification NFF 16-101, Smoke index: F1, Flammability class: I2