


Number of contacts

78+2, 60+4, 42+6, 24+8



Female connectors

DIN Signal
up to 2 A

Identification	No. of contacts	Contact arrangement	Performance levels according to IEC 60603-2. Explanation chapter 00			
			3	2	1	
Female connector with solder pins 2.9 mm (without special contacts)	78 + 2		Performance level 3 on request	09 03 278 6804		
	60 + 4			09 03 260 6804		
	42 + 6			09 03 242 6804		
	24 + 8			09 03 224 6804		
Female connector with solder pins 4.5 mm (without special contacts)	78 + 2			09 03 278 6805		
	60 + 4			09 03 260 6805		
	42 + 6			09 03 242 6805		
	24 + 8			09 03 224 6805		
Female connector with solder pins 13 mm (without special contacts)	78 + 2			09 03 278 6401		
	60 + 4			09 03 260 6401		
	42 + 6			09 03 242 6401		
	24 + 8			09 03 224 6401		
Female connector with press-in pins 4.5 mm (without special contacts)	78 + 2			09 03 278 6850		09 03 278 2850
	60 + 4			09 03 260 6850		
	42 + 6			09 03 242 6850		
	24 + 8			09 03 224 6850		