


Number of contacts

20



Male connectors

Identification	No. of contacts	Contact arrangement	Part number	Performance levels according to IEC 60603-2. Explanation chapter 00		
				3	2	1
Male connector with solder pins 2.5 mm with fixing flange with fixing flange, THR with fixing flange, THR, 240 pieces on a reel without fixing flange without fixing flange, THR without fixing flange, THR, 240 pieces on a reel	20		Performance level 3 on request	09 75 120 6902	Performance level 1 on request	
	20			09 75 120 6519 ^{d)} 09 75 120 6519 792 ^{d)}		
	20			09 75 120 6592		
	20			09 75 120 6569 ^{d)} 09 75 120 6569 792 ^{d)}		
Male connector with solder pins 4.0 mm with fixing flange with fixing flange, THR without fixing flange without fixing flange, THR	20			09 75 120 6903		
	20			09 75 120 6520 ^{d)}		
	20			09 75 120 6593		
	20			09 75 120 6570 ^{d)}		
Male connector with solder pins 13 mm with fixing flange with fixing flange, THR	20			09 75 120 6577		
	20			09 75 120 6521 ^{d)}		
Male connector with wrap posts¹⁾ 13 mm with fixing flange	20			09 75 120 6907		
Male connector with press-in pins 5.0 mm with fixing flange without fixing flange	20			09 75 120 6904		
	20		09 75 120 6504			

¹⁾ To be used only for wire wrap termination

^{d)} CTI > 400