

Number of contacts

16+

16 A 250 V 4 kV 3

Han A

Identification	Conductor cross-section (mm <sup>2</sup> )	Part number		Drawing (dimensions in mm)
		Male	Female	
<p>Han A®, Crimp termination</p> <p>Please order crimp contacts separately.</p>	0.14 ... 4	09 20 016 3001	09 20 016 3101	<p>1) Distance for contact max. 24 mm</p>
<p>Han A®, Screw termination, Contact surface: Silver plated</p>	0.75 ... 2.5	09 20 016 2612	09 20 016 2812	<p>1) Distance for contact max. 24 mm Stripping length 7.5 mm Tightening torque 0.5 Nm</p>
<p>Han A®, Screw termination, With wire protection, Contact surface: Silver plated</p>	0.75 ... 2.5	09 20 016 2614	09 20 016 2814	<p>Contact arrangement (view from termination side)</p> <p>Panel cut out for use without Hoods/Housings</p>