






Number of contacts

**32+**

16 A 250 V 4 kV 3

Identification	Conductor cross-section (mm <sup>2</sup> )	Part number		Drawing (dimensions in mm)
		Male	Female	
<p>Han A®, Crimp termination, 1 ... 16</p>  <p>Please order crimp contacts separately. You need two inserts for a complete assembly!</p>	0.14 ... 4	09 20 016 3001	09 20 016 3101	 <p>1) Distance for contact max. 24 mm</p>
<p>Han A®, Continuing marking, Crimp termination, 17 ... 32</p>  <p>Please order crimp contacts separately. You need two inserts for a complete assembly!</p>	0.14 ... 4	09 20 016 3011	09 20 016 3111	 <p>M F</p> <p>Contact arrangement (view from termination side)</p>  <p>Panel cut out for use without Hoods/Housings</p>