







Number of contacts

6+

16 A 500 V 6 kV 3

Han E/EE

Identification	Conductor cross-section (mm ²)	Part number		Drawing (dimensions in mm)	
		Male	Female		
<p>Han® ES, Cage-clamp termination, Contact surface: Silver plated</p> 	0.14 ... 2.5	09 33 006 2616	09 33 006 2716	 <p>1) distance for contact max. 21 mm</p>	
<p>Han® ES Press, Cage-clamp termination, Contact surface: Silver plated</p>  <p>Blue slide for hoods/housings high construction only</p>	0.14 ... 2.5	09 33 006 2648	09 33 006 2748	 <p>Distance for contact max. 21 mm</p>	 <p>Contact arrangement (view from termination side)</p>  <p>Panel cut out</p>