





Han E/
EE

Identification	Conductor cross-section (mm ²)	Part number		Drawing (dimensions in mm)
		Male	Female	
<p>Han® ESS, Cage-clamp termination, 1 ... 24</p> <p>Contact surface: Silver plated</p>  <p>two terminations per contact for hoods/housings high construction only You need two inserts for a complete assembly!</p>	0.14 ... 2.5	09 33 024 2672	09 33 024 2772	 <p>1) distance for contact max. 21 mm</p>  <p>M F</p> <p>Contact arrangement (view from termination side)</p>  <p>Panel cut out</p>