

Number of contacts

**16+**

16 A 500 V 6 kV 3

Han E/  
EE

Identification	Conductor cross-section (mm <sup>2</sup> )	Part number		Drawing (dimensions in mm)
		Male	Female	
<p>Han E®, Crimp termination</p> <p>Please order crimp contacts separately.</p>	0.14 ... 4	09 33 016 2602	09 33 016 2702	<p>1) distance for contact max. 21 mm</p>
<p>Han E®, Screw termination, With wire protection, Contact surface: Silver plated</p>	0.75 ... 2.5	09 33 016 2601	09 33 016 2701	<p>1) distance for contact max. 21 mm</p> <p>1 10 2 9 2 10 3 11 3 11 4 12 4 12 5 13 5 13 6 14 6 14 7 15 7 15 8 16 8 16</p> <p>M F</p> <p>Contact arrangement (view from termination side)</p> <p>Panel cut out</p>