

Number of contacts

3+

16 A 830 V 8 kV 3
+ 2 additional relay contacts

Han
Hv E

| Identification | Conductor cross-section (mm ²) | Part number | | Drawing (dimensions in mm) |
|---|--|----------------|----------------|--|
| | | Male | Female | |
| Han® Hv ES, Cage-clamp termination, Contact surface: Silver plated | 0.14 ... 2.5 | 09 34 003 2616 | 09 34 003 2716 | <p>M F</p> <p>Contact arrangement (view from termination side) Han® 3 Hv ES</p> <ul style="list-style-type: none"> ◆ Power contacts ● Relay contact ○ Without contact <p>Panel cut out for use without Hoods/Housings</p> |