

Number of contacts

6+

16 A 830 V 8 kV 3
+ 2 additional relay contacts

Han
Hv E

Identification	Conductor cross-section (mm ²)	Part number		Drawing (dimensions in mm)
		Male	Female	
<p>Han® Hv ES, Cage-clamp termination, Contact surface: Silver plated</p>	0.14 ... 2.5	09 34 006 2616	09 34 006 2716	<p> M F Contact arrangement (view from termination side) Han® 6 Hv ES • Power contacts ● Relay contact ○ Without contact </p> <p>Panel cut out for use without Hoods/Housings</p>