

Number of contacts

3+

16 A 830 V 8 kV 3
+ 2 additional relay contacts

Han
Hv E

Identification	Conductor cross-section (mm ²)	Part number		Drawing (dimensions in mm)				
		Male	Female					
<p>Han Hv E®, Crimp termination</p> <p>Please order crimp contacts separately.</p>	0.5 ... 4	09 34 003 2602	09 34 003 2702					
<p>Han Hv E®, Screw termination, With wire protection, Contact surface: Silver plated</p>	0.75 ... 2.5	09 34 003 2601	09 34 003 2701					
<table border="0" style="width: 100%;"> <tr> <td style="text-align: center;"> </td> <td style="text-align: center;"> </td> </tr> <tr> <td style="text-align: center;">M</td> <td style="text-align: center;">F</td> </tr> </table> <p>Contact arrangement (view from termination side) Han® 3 Hv E ◆ Power contacts ● Relay contact ○ Without contact</p> <p>Panel cut out for use without Hoods/Housings</p>							M	F
M	F							