




Number of contacts

4+

80 A 830 V 8 kV 3
 16 A 400 V 6 kV 3
 + 2 additional signal contacts

Han-Com

Identification	Conductor cross-section (mm ²)	Part number		Drawing (dimensions in mm)																								
		Male	Female																									
Han-Com®, Han® K 4/2, Screw termination, Contact surface: Silver plated 	1.5 ... 16, 0.5 ... 2.5 Signal	09 38 006 2601	09 38 006 2701	 <p>1) distance for contact max. 21 mm</p>  <p>11 3 2 12 4 1 2 12</p> <p>M F</p> <p>Contact arrangement (view from termination side)</p> <table border="1"> <thead> <tr> <th colspan="3">Power contacts</th> </tr> <tr> <th>Conductor cross-section</th> <th>Tightening torque</th> <th>Stripping length</th> </tr> </thead> <tbody> <tr> <td>1.5 mm²</td> <td>1.2 Nm</td> <td>14 mm</td> </tr> <tr> <td>2.5 mm²</td> <td>2 Nm</td> <td>14 mm</td> </tr> <tr> <td>4 mm²</td> <td>3 Nm</td> <td>14 mm</td> </tr> <tr> <td>6 mm²</td> <td>3 Nm</td> <td>14 mm</td> </tr> <tr> <td>10 mm²</td> <td>3 Nm</td> <td>14 mm</td> </tr> <tr> <td>16 mm²</td> <td>3 Nm</td> <td>14 mm</td> </tr> </tbody> </table> <p>Signal contacts : Stripping length 7.5 mm Tightening torque 0.5 Nm</p>	Power contacts			Conductor cross-section	Tightening torque	Stripping length	1.5 mm ²	1.2 Nm	14 mm	2.5 mm ²	2 Nm	14 mm	4 mm ²	3 Nm	14 mm	6 mm ²	3 Nm	14 mm	10 mm ²	3 Nm	14 mm	16 mm ²	3 Nm	14 mm
Power contacts																												
Conductor cross-section	Tightening torque	Stripping length																										
1.5 mm ²	1.2 Nm	14 mm																										
2.5 mm ²	2 Nm	14 mm																										
4 mm ²	3 Nm	14 mm																										
6 mm ²	3 Nm	14 mm																										
10 mm ²	3 Nm	14 mm																										
16 mm ²	3 Nm	14 mm																										