





Han
HsB

Identification	Conductor cross-section (mm ²)	Part number		Drawing (dimensions in mm)
		Male	Female	
Han® HsB, Screw termination, With wire protection, Contact surface: Silver plated 	1.5 ... 6	09 31 006 2601	09 31 006 2701	 <p>1) distance for contact max. 21 mm Tightening torque Clamping screw 1.2 Nm</p>  <p>M F Contact arrangement (view from termination side)</p>  <p>Panel cut out for use without Hoods/Housings</p>