







Number of contacts

10+

16 A 500 V 6 kV 3

Han AV

Identification	Conductor cross-section (mm ²)	Part number		Drawing (dimensions in mm)	
		Male	Female		
Han E® AV, Terminal block connector, Left hand version, Multi contour (MK), Screw termination, Contact surface: Silver plated 	0.2 ... 2.5	09 33 010 4625	09 33 010 4725		
					
Han E® AV, Terminal block connector, Left hand version, Single contour (SK), Screw termination, Contact surface: Silver plated 	0.2 ... 2.5	09 33 010 4626	09 33 010 4726	