







Number of contacts

# 4

40 A 830 V 8 kV 3

Han Q

Identification	Conductor cross-section (mm <sup>2</sup> )	Part number		Drawing (dimensions in mm)																		
		Male	Female																			
<p>Han® Q, 4/0, Crimp termination</p>  <p>Please order crimp contacts separately.</p>	1.5 ... 10	09 12 004 3051	09 12 004 3151																			
<p>Han® C, Crimp contact, Contact surface: Silver plated</p> 	1.5 2.5 4 6 10	09 32 000 6104 09 32 000 6105 09 32 000 6107 09 32 000 6108 09 32 000 6109	09 32 000 6204 09 32 000 6205 09 32 000 6207 09 32 000 6208 09 32 000 6209																			
<p>Coding element, Pack contents: 20 pieces per frame</p> 		09 12 000 9924																				
				<table border="1"> <thead> <tr> <th>Conductor cross-section</th> <th>∅</th> <th>Stripping length</th> </tr> </thead> <tbody> <tr> <td>1.5 mm<sup>2</sup> AWG 16</td> <td>1.75 mm</td> <td>9.5 mm</td> </tr> <tr> <td>2.5 mm<sup>2</sup> AWG 14</td> <td>2.25 mm</td> <td>9.5 mm</td> </tr> <tr> <td>4 mm<sup>2</sup> AWG 12</td> <td>2.85 mm</td> <td>9.5 mm</td> </tr> <tr> <td>6 mm<sup>2</sup> AWG 10</td> <td>3.5 mm</td> <td>9.5 mm</td> </tr> <tr> <td>10 mm<sup>2</sup> AWG 8</td> <td>4.3 mm</td> <td>12 mm</td> </tr> </tbody> </table>	Conductor cross-section	∅	Stripping length	1.5 mm <sup>2</sup> AWG 16	1.75 mm	9.5 mm	2.5 mm <sup>2</sup> AWG 14	2.25 mm	9.5 mm	4 mm <sup>2</sup> AWG 12	2.85 mm	9.5 mm	6 mm <sup>2</sup> AWG 10	3.5 mm	9.5 mm	10 mm <sup>2</sup> AWG 8	4.3 mm	12 mm
Conductor cross-section	∅	Stripping length																				
1.5 mm <sup>2</sup> AWG 16	1.75 mm	9.5 mm																				
2.5 mm <sup>2</sup> AWG 14	2.25 mm	9.5 mm																				
4 mm <sup>2</sup> AWG 12	2.85 mm	9.5 mm																				
6 mm <sup>2</sup> AWG 10	3.5 mm	9.5 mm																				
10 mm <sup>2</sup> AWG 8	4.3 mm	12 mm																				