





Number of contacts

5+

16 A 230/400 V 4 kV 3

Identification	Conductor cross-section (mm ²)	Part number		Drawing (dimensions in mm)
		Male	Female	
<p>Han® Q, 5/0, Han-Quick Lock® termination, Contact surface: Silver plated</p>  <p>Blue slide</p>	0.5 ... 2.5	09 12 005 2633	09 12 005 2733	<p>M</p>  <p>F</p>  <p>Stripping length 10 mm</p>
<p>Han® Q, 5/0, Han-Quick Lock® termination, Contact surface: Silver plated</p>  <p>Black slide</p>	0.25 ... 1.5	09 12 005 2634	09 12 005 2734	