

Number of contacts

# 2

10 A 50 V 0.8 kV 3  
+ 4 electrical contacts 10 A + option for PE



Han-Brid

Identification	Part number		Drawing (dimensions in mm)
	Male	Female	
Han-Brid®, Han-Brid® FO, Hybrid field bus connector  Device side FO (f) + Han D® (f) With PCB		09 12 004 2701	<p>Also available as single parts: 09 12 004 3101 Lower part, unloaded</p>
Han-Brid®, Han-Brid® FO, Hybrid field bus connector  Cable side FO (m) + Han D® (m) for POF	09 12 004 2601		<p>09 12 004 3001 Unloaded</p>
Han-Brid®, Han-Brid® FO, Hybrid field bus connector  Cable side With FO contacts FO (m) + Han D® (m) for POF crimpless	09 12 004 2603		<p>09 12 004 3003 Unloaded</p>
Han-Brid®, Han-Brid® FO, Hybrid field bus connector  Cable side FO (m) + Han D® (m) for HCS® fibre	09 12 004 2606		<p>09 12 004 3006 Unloaded</p>