









Number of contacts

2

10 A 24 V 0.8 kV 3
+ RJ45

Han-Brid

Identification	Conductor cross-section (mm ²)	Part number		Drawing (dimensions in mm)
		Male	Female	
Han-Brid®, Han-Brid® RJ45 C, hybrid network connector 	0.12 Stranded 0.22 ... 0.32 Stranded, 0.26 ... 0.32 Solid	09 12 003 3013 09 12 003 3011		
With RJ Industrial Han-Brid®, Han-Brid® RJ45 C, hybrid network connector, 10 Gbit/s 		09 12 003 3015		
With RJ Industrial Han-Brid®, Han-Brid® RJ45 C, hybrid network connector, Cat. 6A 		09 12 003 3016		
With RJ Industrial Han-Brid®, Han-Brid® RJ45 C, hybrid network connector 		09 12 003 3021		
With Stewart RJ45 Han-Brid®, Han-Brid® RJ45 C, hybrid network connector 		09 12 003 3031		
With HIROSE RJ45				