











| Identification | Cable entry | Part number | | Drawing (dimensions in mm) |
|---|------------------|------------------|----------------------------------|--|
| | | Low construction | High construction | |
| <p>Han® M, Bulkhead mounted housing, Rear mounting, IP66</p> <p>Pack contents: Mounting frame is included with- in the delivery</p>  | | 09 37 024 0391 | |  <p>Panel cut out</p> |
| <p>Han® M, Bulkhead mounted housing, Rear mounting, IP66</p>  | | 09 37 024 0392 | |  <p>Panel cut out</p> |
| <p>Han® M, Surface mounted housing, Side entry, IP65</p>  | 2x M32 2x M40 | | 19 37 024 0272 19 37 024 0273 |  |
| <p>Han® M, Cable to cable housing, Side entry, IP65</p>  | 1x M40 | | 19 37 024 0733 |  |
| <p>Han® M, Protection cover, for hoods, Metal, With fixing cord, IP65</p>  | | 09 37 024 5402 | 09 37 024 5402 |  |