








Standard hoods/housings for industrial connectors  
Single locking lever

Identification	Cable entry	Part number		Drawing (dimensions in mm)	
		Low construction	High construction		
Han® B, Hood, Top entry, IP65, IP66, IP67  	1x M20 1x M25 1x M32 1x M40 2x M20	19 30 010 1440 19 30 010 1441	19 30 010 0447 19 30 010 0448 19 30 010 0495	 	
Han® B, Hood, Side entry, IP65, IP66, IP67  	1x M20 1x M25 1x M32	19 30 010 1540 19 30 010 1541	19 30 010 0547	 	
Han® B, Hood, Without cable entry, IP65, IP66, IP67  			09 30 010 0803	