






Accessories

Technical characteristics

Material (accessories) Thermoplastic

Technical characteristics

Colour (accessories) Black
RoHS compliant

Identification	Clamping range (mm)	Part number	Drawing (dimensions in mm)
Cable entry seal 	3 ... 4	09 00 000 5351	
	4 ... 5	09 00 000 5352	
	5 ... 6	09 00 000 5353	
	6 ... 7	09 00 000 5354	
	7 ... 8	09 00 000 5355	
	8 ... 9	09 00 000 5356	
	9 ... 10	09 00 000 5357	
Cable entry seal, Additional strain relief can be provided by cable ties (max. width 8 mm) 	10 ... 11	09 00 000 5358	
	11 ... 12	09 00 000 5359	
	12 ... 13	09 00 000 5360	
	13 ... 14	09 00 000 5361	
	14 ... 15	09 00 000 5362	
	15 ... 16	09 00 000 5363	
Cable entry seal, for ASI cable 		09 00 000 5364	
Dummy plugs 		09 00 000 5350	