






Number of contacts

# 32+

10 A 250 V 4 kV 2  
 4 A 50 V 0.8 kV 2  
 + 55 additional signal contacts

Han-Com

Identification	Conductor cross-section (mm <sup>2</sup> )	Part number		Drawing (dimensions in mm)																												
		Male	Female																													
Han-Com®, Han® K 32/55, Crimp termination  Please order crimp contacts separately.	0.14 ... 2.5, 0.09 ... 0.52 Signal	09 38 087 3001	09 38 087 3101	 1) distance for contact max. 21 mm  Contact arrangement (view from termination side)  <table border="1"> <thead> <tr> <th>Conductor cross-section</th> <th>AWG</th> <th>Ø</th> <th>Stripping length</th> </tr> </thead> <tbody> <tr> <td>0.14-0.37 mm<sup>2</sup></td> <td>AWG 26-22</td> <td>0.9 mm</td> <td>8 mm</td> </tr> <tr> <td>0.5 mm<sup>2</sup></td> <td>AWG 20</td> <td>1.1 mm</td> <td>8 mm</td> </tr> <tr> <td>0.75 mm<sup>2</sup></td> <td>AWG 18</td> <td>1.3 mm</td> <td>8 mm</td> </tr> <tr> <td>1 mm<sup>2</sup></td> <td>AWG 18</td> <td>1.45 mm</td> <td>8 mm</td> </tr> <tr> <td>1.5 mm<sup>2</sup></td> <td>AWG 16</td> <td>1.75 mm</td> <td>8 mm</td> </tr> <tr> <td>2.5 mm<sup>2</sup></td> <td>AWG 14</td> <td>2.25 mm</td> <td>6 mm</td> </tr> </tbody> </table>	Conductor cross-section	AWG	Ø	Stripping length	0.14-0.37 mm <sup>2</sup>	AWG 26-22	0.9 mm	8 mm	0.5 mm <sup>2</sup>	AWG 20	1.1 mm	8 mm	0.75 mm <sup>2</sup>	AWG 18	1.3 mm	8 mm	1 mm <sup>2</sup>	AWG 18	1.45 mm	8 mm	1.5 mm <sup>2</sup>	AWG 16	1.75 mm	8 mm	2.5 mm <sup>2</sup>	AWG 14	2.25 mm	6 mm
Conductor cross-section	AWG	Ø	Stripping length																													
0.14-0.37 mm <sup>2</sup>	AWG 26-22	0.9 mm	8 mm																													
0.5 mm <sup>2</sup>	AWG 20	1.1 mm	8 mm																													
0.75 mm <sup>2</sup>	AWG 18	1.3 mm	8 mm																													
1 mm <sup>2</sup>	AWG 18	1.45 mm	8 mm																													
1.5 mm <sup>2</sup>	AWG 16	1.75 mm	8 mm																													
2.5 mm <sup>2</sup>	AWG 14	2.25 mm	6 mm																													
Han D®, Crimp contact, Contact surface: Silver plated 	0.14 ... 0.37 0.5 0.75 1 1.5 2.5	09 15 000 6104 09 15 000 6103 09 15 000 6105 09 15 000 6102 09 15 000 6101 09 15 000 6106	09 15 000 6204 09 15 000 6203 09 15 000 6205 09 15 000 6202 09 15 000 6201 09 15 000 6206																													