





Number of contacts

# 2

16 A 2.500 V 15 kV 3

Modular

Identification	Conductor cross-section (mm <sup>2</sup> )	Part number		Drawing (dimensions in mm)
		Male	Female	
<p>Han-Modular®, Han® HV module, Single module, Crimp termination,</p> <p>Pack contents: 1 module, 2 locking sleeves, 2 heat shrink tubes</p>  <p>Please order crimp contacts separately.</p>	0.5 ... 4	09 14 002 3025	09 14 002 3125	 <p>Assembly instructions</p>  <p><b>ATTENTION!</b> Stripping length 9.5 mm Crimp with crimping tool 09 99 000 0888 Snap crimped cable in the insert. Shrink the heat shrink tube over the rear of contact.</p>
<p>Han E®, Crimp contact, Contact surface: Silver plated</p> 	0.5 0.75 1 1.5 2.5 3 4	09 33 000 6121 09 33 000 6114 09 33 000 6105 09 33 000 6104 09 33 000 6102 09 33 000 6106 09 33 000 6107	09 33 000 6220 09 33 000 6214 09 33 000 6205 09 33 000 6204 09 33 000 6202 09 33 000 6206 09 33 000 6207	