

## Features

- Compact design saves space
- Practical and easy handling
- Reduction of material and assembly costs

## Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP20
Retention force	200 N Without guiding, 300 N With guiding
Material (accessories)	Polycarbonate (PC)
Colour (accessories)	RAL 7032 (pebble grey)
Material flammability class acc. to UL 94	V-0
RoHS	compliant

## Specifications and approvals

IEC 60068-2-6 Vibration (sinusoidal)  
IEC 60068-2-27 Shock

## Details

Inserts can be mounted on the panel mounting part and the latching part with the standard insert mounting screws.

High mechanical security of the fixings.

No functional impairment is caused by slight over tightening of the fixing screws.

Alternatively, Han® coding elements (code pins or guide pins and bushes) may be used.

Label 9 x 20 mm may be fitted in both sides of each latching element. Label 7 x 20 mm may be fitted to the top of the latching part without the strain relief element.

Up to 2 cable ties with max. 5 mm width can be used on the strain relief.

Please note: The strain relief element should be assembled to the latching part at the end of the insert opposite to the ground screw.

### Identification

Han-Snap®,  
Latching parts,  
IP20


Pack contents:  
2 latching parts



### Part number

09 33 000 9987

### Drawing (dimensions in mm)



- ① Slot for identification strip 9 x 20
- ② Slot for identification strip 7 x 20

6 B: a= 78.5  
10 B: a= 91.5  
16 B: a= 112.5  
24 B: a= 138.5