





Number of contacts

# 3+

200 A 1.150/2.000 V 8 kV 3  
 16 A 400 V 6 kV 3  
 + 2 additional signal contacts

Han  
 HC

Identification	Conductor cross-section (mm <sup>2</sup> )	Part number		Drawing (dimensions in mm)
		Male	Female	
Han-Com®, Han® K 3/2, Straight, Axial screw termination / screw termination, Contact surface: Silver plated 	35 ... 70, 0.5 ... 2.5 Signal, 16 ... 35 PE	09 38 005 2601	09 38 005 2701	 <p>Distance for contact max. 21 mm                      Stripping length 22 mm                      Tightening torque 8 Nm @ 35 mm<sup>2</sup>, 9 Nm @ 50 mm<sup>2</sup>, 10 Nm @ 70 mm<sup>2</sup>                      Signal contacts: Stripping length 7 mm,                      Tightening torque 0.5 Nm                      PE contact: Stripping length 14 mm, Tightening torque 6 Nm</p>
Han-Com®, Han® K 3/2, Angled, Axial screw termination / screw termination, Contact surface: Silver plated 	35 ... 70, 0.5 ... 2.5 Signal, 16 ... 35 PE	09 38 005 2602	09 38 005 2702	 <p>Distance for contact max. 21 mm                      Stripping length 22 mm                      Tightening torque 8 Nm @ 35 mm<sup>2</sup>, 9 Nm @ 50 mm<sup>2</sup>, 10 Nm @ 70 mm<sup>2</sup>                      Signal contacts: Stripping length 7 mm,                      Tightening torque 0.5 Nm                      PE contact: Stripping length 14 mm, Tightening torque 6 Nm</p>