





Hoods/housings for rough environments  
Single locking lever

Han  
HC

Identification	Cable entry	Part number High construction	Drawing (dimensions in mm)
<p>Han® M, Hood, Top entry, IP65</p> 	<p>4x M25</p>	<p>19 37 048 0401</p>	
<p>Han® M, Frame, for male inserts, for female inserts, 4x HC 350 contacts + 2x Han® Q 5/0 in a hood</p> 		<p>09 11 000 9954</p>	 <p>Tightening torque Fixing screws M3: 0.5 Nm Tightening torque Fixing screws Han® Q 5/0: 0.25 Nm Tightening torque Cross-tying screws 1.5 Nm</p>