




Number of contacts

25

4 A 50 V 0.8 kV 3

Han
HMC

Identification	Conductor cross-section (mm ²)	Part number		Drawing (dimensions in mm)												
		Male	Female													
Han-Modular®, Han® High Density module, Crimp termination  <p>Please order crimp contacts separately.</p>	0.09 ... 0.52	09 14 025 3001	09 14 025 3101	 <p>Contact arrangement (view from termination side)</p> <table border="1"> <thead> <tr> <th>導体断面積</th> <th>φ</th> <th>ストリップ長さ</th> </tr> </thead> <tbody> <tr> <td>0.08 - 0.21 mm²</td> <td>AWG 28-24</td> <td>4 mm</td> </tr> <tr> <td>0.13 - 0.33 mm²</td> <td>AWG 26-22</td> <td>4 mm</td> </tr> <tr> <td>0.33 - 0.52 mm²</td> <td>AWG 22-20</td> <td>4 mm</td> </tr> </tbody> </table>	導体断面積	φ	ストリップ長さ	0.08 - 0.21 mm ²	AWG 28-24	4 mm	0.13 - 0.33 mm ²	AWG 26-22	4 mm	0.33 - 0.52 mm ²	AWG 22-20	4 mm
導体断面積	φ	ストリップ長さ														
0.08 - 0.21 mm ²	AWG 28-24	4 mm														
0.13 - 0.33 mm ²	AWG 26-22	4 mm														
0.33 - 0.52 mm ²	AWG 22-20	4 mm														
D-Sub, Crimp contact, Contact surface: HMC gold plated 	0.08 ... 0.21 0.13 ... 0.33 0.33 ... 0.52	09 67 000 7570 09 67 000 5570 09 67 000 8570	09 67 000 7470 09 67 000 5470 09 67 000 8470													