

Number of contacts

# 16+

16 A 500 V 6 kV 3

Han  
HMC

Identification	Conductor cross-section (mm <sup>2</sup> )	Part number		Drawing (dimensions in mm)																
		Male	Female																	
<p>Han® ES Press HMC, Cage-clamp termination, Contact surface: HMC gold plated</p> <p>for hoods/housings high construction only Blue slide</p>	0.14 ... 2.5	09 33 216 2648	09 33 216 2748	<p>Distance for contact max. 21 mm</p> <p> <table border="0"> <tr><td>9 ● 1</td><td>1 ● 9</td></tr> <tr><td>10 ● 2</td><td>2 ● 10</td></tr> <tr><td>11 ● 3</td><td>3 ● 11</td></tr> <tr><td>12 ● 4</td><td>4 ● 12</td></tr> <tr><td>13 ● 5</td><td>5 ● 13</td></tr> <tr><td>14 ● 6</td><td>6 ● 14</td></tr> <tr><td>15 ● 7</td><td>7 ● 15</td></tr> <tr><td>16 ● 8</td><td>8 ● 16</td></tr> </table> </p> <p>M F</p> <p>Contact arrangement (view from termination side)</p> <p>Panel cut out</p>	9 ● 1	1 ● 9	10 ● 2	2 ● 10	11 ● 3	3 ● 11	12 ● 4	4 ● 12	13 ● 5	5 ● 13	14 ● 6	6 ● 14	15 ● 7	7 ● 15	16 ● 8	8 ● 16
9 ● 1	1 ● 9																			
10 ● 2	2 ● 10																			
11 ● 3	3 ● 11																			
12 ● 4	4 ● 12																			
13 ● 5	5 ● 13																			
14 ● 6	6 ● 14																			
15 ● 7	7 ● 15																			
16 ● 8	8 ● 16																			