





Number of contacts

55+

10 A 250 V 4 kV 3

Han D

Identification	Conductor cross-section (mm ²)	Part number		Drawing (dimensions in mm)
		Male	Female	
<p>Han® DDD, Crimp termination</p>  <p>PE connection with a Han D® crimp contact Please order crimp contacts separately.</p>	0.14 ... 2.5	09 16 055 2001	09 16 055 2101	 <p>1) distance for contact max. 21 mm</p>  <p>Contact arrangement (view from termination side)</p>  <p>Panel cut out for use without Hoods/Housings</p>