















Han Eco

40 A		<b>Han® A Crimp module</b>	<b>Han® C module</b>	<b>Han® CC module</b>	<b>Han® CD module</b>
					
	Number of contacts	2	3	4	3 + 4
	Electrical data	40 A / 1000 V	40 A / 690 V	40 A / 830 V	40 A + 10 A / 830 V
	Cross-section	1.5 ... 10 mm <sup>2</sup>	1.5 ... 6 mm <sup>2</sup>	1.5 ... 6 mm <sup>2</sup>	0.14 ... 6 mm <sup>2</sup>
Termination type	Crimp termination, Han® C				
Male module (M)	09 14 002 3002	09 14 003 3001	09 14 004 3041	09 14 007 3001	
Female module (F)	09 14 002 3102	09 14 003 3101	09 14 004 3141	09 14 007 3101	
16 A		<b>Han E® module</b>	<b>Han® EE module</b>	<b>Han® EEE module</b>	<b>Han E® Protected module</b>
					
	Number of contacts	6	8	20*	6
	Electrical data	16 A / 500 V	16 A / 400 V	16 A / 500 V	16 A / 830 V
	Cross-section	0.14 ... 4 mm <sup>2</sup>	0.14 ... 4 mm <sup>2</sup>	0.14 ... 4 mm <sup>2</sup>	0.14 ... 4 mm <sup>2</sup>
Termination type	Crimp termination, Han E®				
Male module (M)	09 14 006 3001	09 14 008 3001	09 14 020 3001	09 14 006 3041	
Female module (F)	09 14 006 3101	09 14 008 3101	09 14 020 3101	09 14 006 3141	
≤ 10 A		<b>Han DD® module</b>	<b>Han® DDD module</b>	<b>Han DD® Quad module</b>	
					
	Number of contacts	12	17	25	
	Electrical data	10 A / 250 V	10 A / 150 V	4 A / 50 V	
	Cross-section	0.14 ... 2.5 mm <sup>2</sup>	0.14 ... 2.5 mm <sup>2</sup>	0.08 ... 0.52 mm <sup>2</sup>	
Termination type	Crimp termination, Han D®			Crimp termination, D-Sub	
Male module (M)	09 14 012 3002	09 14 017 3001	09 14 025 3001		
Female module (F)	09 14 012 3102	09 14 017 3101	09 14 025 3101		
High voltage		<b>Han® HV module 40 A</b>	<b>Han® HV module 16 A</b>	<b>Han® HV Single module</b>	
					
	Number of contacts	2*	2*	2	
	Electrical data	40 A / 2900/5000 V	16 A / 2900/5000 V	16 A / 2500 V	
	Cross-section	1.5 ... 10 mm <sup>2</sup>	0.14 ... 4 mm <sup>2</sup>	0.14 ... 4 mm <sup>2</sup>	
Termination type	Crimp termination, Han® C			Crimp termination, Han E®	
Male module (M)	09 14 002 3023	09 14 002 3021	09 14 002 3025		
Female module (F)	09 14 002 3123	09 14 002 3121	09 14 002 3125		

\* Double module, requires two places in the frame