







Double locking lever

Han Eco

Identification	Cable entry	Clamping range (mm)	Part number	Drawing (dimensions in mm)
<p>Han-Eco® Modular, Hood, With integrated cable gland, Top entry, IP65</p> 	<p>1x M32 1x M40</p>	<p>13 ... 21 16 ... 28</p>	<p>19 41 106 0422 19 41 106 0423</p>	
<p>Han-Eco® Modular, Hood, With integrated cable gland, Side entry, IP65</p> 	<p>1x M32</p>	<p>13 ... 21</p>	<p>19 41 106 0522</p>	
<p>Han-Eco® Modular, Bulkhead mounted housing, IP65</p> 			<p>19 41 006 0301</p>	 <p>Panel cut out</p>