







Identification	Cable entry	Clamping range (mm)	Part number	Drawing (dimensions in mm)
<p>Han-Eco® Modular, Surface mounted housing, With integrated cable gland, Side entry, IP65</p> 	<p>1x M40 2x M40</p>	<p>16 ... 28 16 ... 28</p>	<p>19 41 316 0233 19 41 316 0273</p>	
<p>Han-Eco® Modular, Cable to cable housing, With integrated cable gland, Top entry, IP65</p> 	<p>1x M40</p>	<p>16 ... 28</p>	<p>19 41 316 0723</p>	
<p>Han-Eco® Modular, Protection cover, for hoods, IP65</p>  <p>Han-Eco® Modular, Protection cover, for hoods, With fixing cord (loop), IP65</p> 			<p>19 41 216 5406</p> <p>19 41 216 5407</p>	