







Single locking lever



Han
Eco

Identification	Cable entry	Clamping range (mm)	Part number	Drawing (dimensions in mm)
Han-Eco® A, Hood, With integrated cable gland, Top entry, IP65 	1x M20 1x M25	6 ... 13 9 ... 17	19 46 116 0445 19 46 116 0446	
Han-Eco® A, Hood, With integrated cable gland, Side entry, IP65 	1x M20 1x M25	6 ... 13 9 ... 17	19 46 116 0545 19 46 116 0546	
Han-Eco® A, Bulkhead mounted housing, IP65 			19 46 016 0301	 <p>Panel cut out Front mounting / Rear mounting</p>