







Number of contacts

24+

16 A 500 V 6 kV 3

Identification	Conductor cross-section (mm <sup>2</sup> )	Part number		Drawing (dimensions in mm)
		Male	Female	
<p>Han E®, Crimp termination</p>  <p>Please order crimp contacts separately.</p>	0.14 ... 4	09 33 024 2602	09 33 024 2702	 <p>1) distance for contact max. 21 mm</p>
<p>Han E®, Screw termination, With wire protection, Contact surface: Silver plated</p> 	0.75 ... 2.5	09 33 024 2601	09 33 024 2701	 <p>1) distance for contact max. 21 mm</p>
				 <p>M F</p> <p>Contact arrangement (view from termination side)</p>  <p>Panel cut out</p>