



## Derating



### Han® ES Press



- ① Han® 6 ES Press
- ② Han® 10 ES Press
- ③ Han® 16 ES Press Han® 32 ES Press
- ④ Han® 24 ES Press Han® 48 ES Press

## Derating

### Han® ESS



- ① Han® 6 ESS
- ② Han® 10 ESS
- ③ Han® 16 ESS Han® 32 ESS
- ④ Han® 24 ESS Han® 48 ESS

## Specifications and approvals

EN 60664-1  
 IEC 61984  
 UL 1977 ECBT2.E235076  
 UL 2237 PVVA2.E318390  
 CSA-C22.2 No. 182.3 PVVA8.E318390  
 DNV GL  
 CSA-C22.2 No. 182.3 ECBT8.E235076

## Details

Internal use in the switch cabinet in conjunction with Han-Snap® (see chapter Han 11)

Suitable for hoods/housings of series Han® B, Han® M, Han® EMC, Han® HPR, Han® Easy Hood (see chapter Han 31)

Tightening torque 0.5 Nm

Tightening torque PE screw 1.2 Nm