








Standard hoods/housings for industrial connectors  
Single locking lever

Housings

Identification	Cable entry	Part number		Drawing (dimensions in mm)	
		Low construction	High construction		
Han® B, Hood, Top entry, IP65, IP66, IP67  	1x M20 1x M25 1x M32	19 30 006 1440	19 30 006 0446		
			19 30 006 0447		
Han® B, Hood, Side entry, IP65, IP66, IP67  	1x M20 1x M25 1x M32	19 30 006 1540 19 30 006 1541	19 30 006 0546		
			19 30 006 0547		
Han® B, Hood, Without cable entry, IP65, IP66, IP67  			09 30 006 0801	